

STRONGHOLD™

StrongHold™ PVC Electrical Tape designed to support contractors and the way they work



Reliable-Convenient-Economical

StrongHold™ Electrical PVC Vinyl Tape Full Line Offering

With over 25 varieties of tape designed for insulating, bundling and identifying in various indoor/outdoor environments, we are confident that we have all your application needs covered.

StrongHold™ offerings are committed to providing the contractor with reliable convenient, economical products to support their installations.

Not sure which grade of tape is necessary for your application?
Take a look at our chart to compare options.

Heavy Duty



ST88

Professional Grade



ST35






















ST43

General Purpose



ST14

ST17

	HEAVY DUTY	PROFESSIONAL	GENERAL PURPOSE
Thickness	 8.5 mil	 7.0 mil	 7.0 mil
Low temperature rating	 0°F -18°C	 0°F -18°C	 14°F -10°C
High temperature rating	 221°F 105°C	 221°F 105°C	 176°F 80°C
Sticking power (adhesion to steel at 72°F)	 2.2 N/cm TYP	 2.2 N/cm TYP	 1.6-1.8 N/cm
Elongation	 300% TYP	 260% TYP	 200% TYP
Breaking strength	 38 N/cm TYP	 30 N/cm TYP	 25 N/cm TYP
Color			

StrongHold™ Electrical PVC Vinyl Tape Full Line Offering

Suitable for primary insulation and splicing up to 600V and can be used as protective jacketing. Our offering protects against an array of abrasive and corrosive materials, while providing quality adhesion properties, as well as resistance of UV rays and cold weather.

Heavy Duty and Professional Grade Tape

ST 88

ST88





Heavy Duty grade that offers easy application for high level performance over a range of temperatures with protection against UV rays, abrasion, water, oil and other corrosive chemicals. Suitable for primary insulation for splicing up to 600V and can be used as protective jacketing.

ST 43

ST43





Pressure sensitive vinyl electrical tape that offers high abrasion resistance with easy application over a range of temperatures. Flame retardant as well as cold resistant, suitable for primary insulation for splicing up to 600V and can be used as protective jacketing.

ST 35

ST35















Available in nine colors for color coding, excellent elasticity and insulating properties. Professional grade designed to handle range of temperatures with protection against abrasion, water, oil and other corrosive chemical. Suitable for primary insulation for splicing up to 600V and can be used as protective jacketing.

Heavy Duty	StrongHold™ Part Numbers	Case Quantity	Min. Order Qty.	Color	Thickness	Dimension
	ST88-075-66BK	100	20	Black	8.5 mil	0.75" x 0.0085" x 66'
	ST88-100-108BK	80	20	Black	8.5 mil	1.0" x 0.0085" x 108'
	ST88-150-66BK	100	20	Black	8.5 mil	1.5" x 0.0085" x 66'
	ST88-200-66BK	40	20	Black	8.5 mil	2.0" x 0.0085" x 66'

Professional Grade	StrongHold™ Part Numbers	Case Quantity	Min. Order Qty.	Color	Thickness	Dimension
	ST35-075-66BU	20	20	Blue	7 mil	0.75" x 0.007" x 66'
	ST35-075-66BR	20	20	Brown	7 mil	0.75" x 0.007" x 66'
	ST35-075-66GY	20	20	Gray	7 mil	0.75" x 0.007" x 66'
	ST35-075-66GR	20	20	Green	7 mil	0.75" x 0.007" x 66'
	ST35-075-66OR	20	20	Orange	7 mil	0.75" x 0.007" x 66'
	ST35-075-66RD	20	20	Red	7 mil	0.75" x 0.007" x 66'
	ST35-075-66VI	20	20	Violet	7 mil	0.75" x 0.007" x 66'
	ST35-075-66WH	20	20	White	7 mil	0.75" x 0.007" x 66'
	ST35-075-66YL	20	20	Yellow	7 mil	0.75" x 0.007" x 66'
	ST43-075-66BK	100	20	Black	7 mil	0.75" x 0.007" x 66'

US Electrical Tape Color Usage Chart

Ground						
Low Voltage						
	Phase A	Phase B	Phase C	Neutral		
	High Voltage					
		Phase A	Phase B	Phase B	Phase C	Neutral






StrongHold™ Product Full Line Offering

StrongHold™ General Purpose Tape

ST 14	ST14	
		<p>Excellent conformability properties and ease of tearing due to high elongation. Non-corrosive and pressure-sensitive adhesive which eliminates the need for catalysts during application. Flame retardant as well as cold resistant. Suitable as a primary insulation when used for splicing up to 600V.</p>
ST 17	ST17	
		<p>Excellent conformability properties and ease of tearing due to high elongation. Non-corrosive and pressure-sensitive adhesive which eliminates the need for catalysts during application. Flame retardant as well as cold resistant. Suitable as a primary insulation when used for splicing up to 600V.</p>
ST 15	ST15	
		<p>Non-corrosive and pressure-sensitive adhesive which eliminates the need for heat, moisture or other catalysts to affect the application. High elongation, nonflammable and able to be used in various weather conditions. Suitable as a primary insulation when used for splicing up to 600V.</p>

General Purpose	StrongHold™ Part Numbers	Case Quantity	Min. Order Qty.	Color	Thickness	Dimension
	ST17-075-66BU	100	20	Blue	7 mil	0.75" x 0.007" x 66'
	ST17-075-66BR	100	20	Brown	7 mil	0.75" x 0.007" x 66'
	ST17-075-66GY	100	20	Gray	7 mil	0.75" x 0.007" x 66'
	ST17-075-66GR	100	20	Green	7 mil	0.75" x 0.007" x 66'
	ST17-075-66OR	100	20	Orange	7 mil	0.75" x 0.007" x 66'
	ST17-075-66RD	100	20	Red	7 mil	0.75" x 0.007" x 66'
	ST17-075-66YL	100	20	Yellow	7 mil	0.75" x 0.007" x 66'
	ST17-075-66VI	100	20	Violet	7 mil	0.75" x 0.007" x 66'
	ST17-075-66WH	100	20	White	7 mil	0.75" x 0.007" x 66'
	ST14-075-60BK	100	20	Black	7 mil	0.75" x 0.007" x 60'
	ST15-075-66GRYL	100	20	Yellow with Green Stripes	5 mil	0.75" x 0.005" x 66'

StrongHold™ Full Product Offering

Nylon Cable Ties	Stainless-Steel Cable Ties	Terminals	Grounding Pigtails	Supports and Fasteners
				

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA
Markham, Ontario
cs-cdn@panduit.com
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
cs-emea@panduit.com
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
cs-ap@panduit.com
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
cs-japan@panduit.com
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
cs-la@panduit.com
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
cs-aus@panduit.com
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300

PANDUIT®

©2020 Panduit Corp.
ALL RIGHTS RESERVED.
SFCB17--SA-ENG replaces
SFCB15--SA-ENG
01/2020