



Panduit Part Number	PES400
Description	Heavy-Duty Metal Marker Plate Embossing System
Software	Easy-Mark Plus
Characters Included	A through Z, 0 through 9, Special Characters @ # % & * () - + : ; , . /
Character Sizes	5mm (BLOCCO font) & 3mm (SIMPLEX 2 font)
Minimum Plate/Tag Size	(LxW): 1.72" x 0.375" (44mm x 9.5mm)
Maximum Plate/Tag Size	(LxW): 3.50" x 2.12" (89mm x 54mm)
Embossing Speed	300+ Plates/Hour
Input Hopper Capacity	200 Plates (0.5mm thickness)
Output Hopper Capacity	200 Plates (0.5mm thickness)
Output Hopper Capacity, 1.72" Long Plates	50 Plates (0.5mm thickness)
Operating Voltage	100V-240V
Operating Frequency	50Hz-60Hz
Operating Temperature	50F - 104F (10C - 40C)
Operating Humidity	20% - 85% Non-Condensing R.H.
Machine Weight	155 Lbs (70 kg)
Machine Dimensions LxWxH	23.6"x35.8"x16.5" (600mm x 910mm x 420mm)
Crate Total Weight	210 Lbs (95 kg)
Crate Dimensions LxWxH	33"x29"x24" (830mm x 730mm x 600mm)



						TITLE PES400 Panduit Embossing Machine	
						CUSTOMER DRAWING	
						ITEM REVISION NAME 00038SAD/00	PANDUIT
						DATASET FILE NAME 00038SAD_DC/00	
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)	
						.x ± .1 (2.54)	.xxx ± .005 (.127)
						.xx ± .01 (.25)	ANGLES ± 5°
00	08/24/17	KEC	JW	RGRO	INITIAL RELEASE	00038SAD_DC	MATERIALS N/A
						DRAWING NUMBER 00038SAD_DC	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	THIRD ANGLE PROJECTION
							SCALE N/A
							SIZE SHT 1 OF 1