

2


1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	LENGTH	WEIGHT	WEIGHT/LENGTH
FR6X4**2 (SEE NOTE 1)	78.74 IN ±.18 IN (2000.0mm ±4.6mm)	9.71 LB (4404g)	1.48 LB/FT (22.0g/cm)
FR6X4**6 (SEE NOTE 1)	72.00 IN ±.18 IN (1828.8mm ±4.6mm)	8.88 LB (4028g)	1.48 LB/FT (22.0g/cm)

NOTES:

- SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
- DIMENSIONS IN PARENTHESES ARE IN METRIC.



B

B



A

A

6	02-25-13	JBN	RTFI	RN	L. REVISED DRAWING BORDER & TITLE BLOCK										37185-82						

TITLE		FIBERRUNNER 6X4 CHANNEL FR6X4**2, FR6X4**6	
ITEM REVISION NAME		CUSTOMER DRAWING	
DATASET FILE NAME		D37185CC/01	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		PANDUIT	
.X ± .XX ± .03 [.8]			
.XXX ± ANGLES ±		MATERIAL: PVC	
THIRD ANGLE PROJECTION		DRAWING NUMBER: 37185-82	
DRAWN BY	DATE	CHK	SCALE
JHNU	05-11-00	NEY	NONE

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE
							JHNU	05-11-00	NEY	NONE		A

2

1

D10100DA/14