

ITEM NUMBER	PART NUMBER	DESCRIPTION	STANDARD PACKAGE QTY.
1	MP300	MP300 PRINTER	1
2	*MP300-ACS	120-240 VAC POWER SUPPLY MODULE WITH POWER CORD FOR NORTH AMERICA	1
3	*MP300-BATT	LITHIUM ION BATTERY	1
4	MP-USB	MP100/300 USB PRINTER CABLE	1
5	*S100X150VAM	MP CASSETTE, SELF-LAMINATING LABEL, VINYL, 1.00" W x 1.50" H, .50" PRINT ON AREA, CLEAR/ WHITE	1
6	IMPORTANT INFORMATION	PRINTED COPY OF IMPORTANT SAFETY INFORMATION SHEET	1
7	QUICK REFERENCE CARD	PRINTED COPY OF QUICK REFERENCE CARD IN THREE LANGUAGES (EN, FR, SP)	1
8	*MP300-CASE	HARD PLASTIC CARRYING CASE WITHOUT SLEEVE	1
9	MP300-MAGNET	SET OF TWO MAGNETIC ATTACHMENTS FOR MP300 PRINTER	1
10	BATTERY DIRECTIVE	BATTERY DIRECTIVE INSTRUCTIONS FOR LITHIUM ION BATTERY PACK	1

△

NOTES:

1. * IN FRONT OF PART NUMBER DENOTES SELLABLE PANDUIT PART NUMBER.



REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
01	1-21-2021	JSUN	RCMC	ALP	△ REMOVE * BEFORE MP300-MAGNET	094056/00
00	10-29-19	TMSA	RCMC	JHAC	INITIAL RELEASE	GAECNXXXX

TITLE		"MP300"	
PANDUIT MP300 MOBILE THERMAL TRANSFER PRINTER		CUSTOMER DRAWING	
ITEM REVISION NAME	00406SBB/01	PANDUIT	MATERIAL: NONE
DATASET FILE NAME	00406SBB_DC/01		
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		DRAWING NUMBER: 00406SBB_DC	
.x ± .1 [2.54]	.xxx ± .005 [.127]	THIRD ANGLE PROJECTION	
.xx ± .01 [.25]	ANGLES ± 5 °	DRAWN BY: TMSA	
DATE: 10-29-19	CHK: JHAC	SCALE: NTS	SIZE: B
SHT 1 OF 1			

D10100DB/17