


PANDUIT P/N	WEIGHT
EA001	0.125kg

SENSOR IDENTIFICATION LABEL



SPECIFICATION:


- 1. STANDARD
 - MEASURING RANGE: 0°C - 65°C [32°F - 149°F]
 - MEASUREMENT ACCURACY: ± 2°C
 - OPERATING RANGE: 0- 65°C, 10-90% RH NON-CONDENSING [32-149°F, 10-90% RH NON-CONDENSING]
 - OPERATIONAL VOLTAGE: 5 ±0.1 VOL TS DC
 - CURRENT DRAW: 30 mA MAX
 - SENSOR HOUSING MATERIAL: ABS, 10% GLASS-FILLED
 - SENSOR HOUSING COLOR: INTERFACE BLACK
 - PLUG: RJ45 COMPLIANT
 - INTERFACE PLUG HOUSING MATERIAL: POLYCARBONATE
 - INTERFACE PLUG HOUSING COLOR: TRANSPARENT
 - LABEL CONTENT: T
- 2. ADDITIONAL: NONE
- 3. ACCESSORY COMPONENTS:
 - CABLE TIES, QTY:(5)
 - INSTALLATION GUIDE, QTY:(1)

NOTES:

- 1. PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSION ARE IN INCHES
- 2. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
- 3. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART

IDENTIFICATION

PART NUMBER	DESCRIPTION
EA001	TEMPERATURE SENSOR KIT



WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.

SIGN _____
DATE _____
PRINT _____

TITLE: SMARTZONE G5 TEMPERATURE SENSOR KIT
CUSTOMER DRAWING

ITEM REVISION NAME: _____
DATASHEET FILE NAME: _____

UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]
Wire Harness Tolerance(mm)

THIRD ANGLE PROJECTION

MATERIAL/COLOR: N/A

0<4<500 ±10
500<4<2000 ±20
2000<4<6000 ±50

DRAWING NUMBER: EA001_DC

SCALE: NONE

SHT 1 OF 1

00A	11/01/2017	Hanson	MM	DJB	INITIAL RELEASE	EA001
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

DRAWN BY: Hanson DATE: 11/01/2017 CHK: MM SCALE: NONE