





Open and Collaborative Work Spaces Demand Robust Infrastructure

Ever-evolving work spaces require an infrastructure that enables on-the-go connectivity, employee accessibility, and individual control of the environment to improve employee productivity. Office workers today may split their time between home and the office, and when in the office, they may share work areas with others rather than having a personal, dedicated space.

Smart building systems make it possible for workers to locate a workspace via an app on their phone, or to register where they are working for the day via a scanner that reads their badge. At the same time, these systems communicate with the building automation system and lights to set the temperature and lighting to the exact levels the worker has said they prefer. Moving around the building? Connectivity is always on thanks to wireless access points and in-building wireless systems.

You can count on Panduit copper cabling systems to deliver data and Power over Ethernet to all of these systems, with simple installation, standards compliance, maximum density, and proven reliability to support collaboration and productivity in your building.



Part Number	Part Description
-------------	------------------

Horizontal Cable	
PUP6AHD04BU-G	Category 6A Vari-MaTriX High Density U/UTP copper cable, plenum, 4-pair, Blue.

Jack Modules and Modular Plugs	
FC-ICCP1MBU	TX6A™ Category 6A UTP FieldCord™ Connector for field termination of 4-pair UTP cable to connect devices with confined port spaces.
FP6X88MTG	TX6A™ Category 6A Field Term Plug for field termination of 4-pair UTP cable. Compatible with Category 6A, Category 6, and Category 5e systems.
FPUD6X88MTG	TX6A™ Category 6A Field Term Plug with up-down angled wire cap for field termination of 4-pair UTP cable. Compatible with Category 6A, Category 6, and Category 5e systems.
CJ6X88TGBU	Category 6A, RJ45, 8-position, 8-wire universal jack module with MaTriX technology, Blue. Supports high-bandwidth applications and is ideal for running next generation Power over Ethernet (PoE++). UL Rated: UL 1863 and UL 2043.
CJUDCAPBU-C	Category 6A 45° angled up/down TG wire cap provides improved cable routing to jacks in confined spaces; 100 pk.

Patch Cords	
UTP28X3BU	Category 6A performance, 28 AWG, UTP patch cord, CM/LSZH, 3 ft., Blue.

Faceplates	
CFPE2IWY	Mini-Com® Executive Series Faceplate, two ports, single-gang, with label and label cover, Off White.
CFFPL2BL	Mini-Com® Modular Furniture Faceplate for standard office furniture openings, two ports; with label and label cover, Black.
CBX2WH-AY	Mini-Com® Surface Mount Box. Two ports, elongated size includes fiber spool; supplied with built-in removable blank, mounting screws, adhesive backing and cable tie, White.

Above Floor Raceway	
AFR4BCBL6	Above floor raceway base and cover, 6 ft., Black. Compatible with a wide range of fittings, couplers, and junction boxes.
AFR4TBLGGL	Above floor raceway table leg fitting to route cable to a desktop or table top, Black.

Zone Architecture	
PZICEA	PanZone® Active In-Ceiling Enclosure with hinged door gas-assist air cylinders; accepts up to 6 RU of standard 19" patch panels, includes mounting brackets and integrated horizontal slack manager, AC power provisions, fan assembly, air dam, and electrical junction box.
CPB24BL	Consolidation Point Enclosure for raised floor, in-ceiling, or wall mount; accepts 19" Mini-Com®, NetKey®, QuickNet™, and fiber Patch Panels, 1 RU.
CPB48BL	Consolidation Point Enclosure for raised floor, in-ceiling, or wall mount; accepts 19" Mini-Com®, NetKey®, QuickNet™, and Fiber Patch Panels, 2 RU.

Physical Security	
SKRJ45RD-X	SmartKeeper RJ45 blockout device, Red.
SKUSBA-V	SmartKeeper USB Type A blockout device, Red.
SKMKEY	SmartKeeper Master Key for use with SmartKeeper blockout devices.

See www.panduit.com for additional colors, sizes, cable jackets, and performance offerings.

