



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




FRONT VIEW
SHOWN W/O DUSTCAPS

SEE SHEETS 2 AND 3 FOR ARTWORK DETAILS

NOTES:

1. SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITIES.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
3. PART NUMBERS:
 - A. SEE SHEET 2 FOR METHOD A.
 - B. SEE SHEET 3 FOR MODIFIED METHOD A, PAIR FLIPPED.
4. METHOD A CASSETTES COMPLY WITH ANSI/TIA-568-C.0. SEE ANSI/TIA-568-C.0 FOR POLARITY DETAILS AND EXAMPLES OF A BASIC LINK.
5. MATERIALS:
 - A. BOX AND LID: PLASTIC
 - B. ADAPTER: COMPOSITE PLASTIC
6. CASSETTE WEIGHT: 4.16oz [118g]
7. DIMENSIONS IN BRACKETS ARE METRIC.




REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
07B	05-28-19	SAT	DWW	EJH	B. ADDED P/N FC29N-24-LAAS & FC29N-24-LAAF.	10F113AB-DC
07A	10-31-17	SAT	JGD	EJH	A. ADDED P/N FC2WA-24-10AS & FC2WA-24-10AF.	10F113AB-DC
R	10-10-12	SAT	TMSE		RELEASED TO PRODUCTION	10F113AB-DC

TITLE 24 FIBER DUPLEX LC CASSETTE METHOD A AND MODIFIED METHOD A, PAIR FLIPPED						
CUSTOMER DRAWING						
ITEM REVISION NAME 10F113AB/07				PANDUIT		
DATASET FILE NAME 10F113AB_DC/07B						
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]				MATERIAL: SEE NOTES		
.x ± .03 [.8]		.xxx ± .005 [.127]		DRAWING NUMBER: 10F113AB-DC		
.xx ± .01 [.25]		ANGLES ± 5 °		THIRD ANGLE PROJECTION		
DRAWN BY SAT	DATE 10-01-12	CHK TMSE	SCALE NONE	SHT 1 OF 3		SIZE A

24 FIBER DUPLEX LC CASSETTE - METHOD A

PART NUMBER	DESCRIPTION
FC2Z0-24-10AS	24 FIBER 50/125um OM4 OPTIMIZED
FC2ZN-24-10AS	24 FIBER 50/125um OM4
FC2X0-24-10AS	24 FIBER 50/125um OM3 OPTIMIZED
FC2XN-24-10AS	24 FIBER 50/125um OM3
FC25N-24-10AS	24 FIBER 50/125um OM2
FC26N-24-10AS	24 FIBER 62.5/125um OM1
FC29N-24-10AS	24 FIBER 9/125um OS1/OS2
FC2SA-24-10AS	24 FIBER 50/125um OM4+, SIGNATURE CORE
FC2WA-24-10AS	24 FIBER 50/125um OM5+, SIGNATURE CORE
FC29N-24-LAAS	24 FIBER OS2 LC/APC, STANDARD LOSS



METHOD A - FIBER LAYOUT


REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 2 OF 3	SIZE
							SAT	10-01-12	TMSE	NONE		A
SEE SHEET 1 FOR REVISION HISTORY							TITLE 24 FIBER DUPLEX LC CASSETTE METHOD A CUSTOMER DRAWING			ITEM REVISION NAME 10F113AB/07		
							DATASET FILE NAME 10F113AB_DC/07B			PANDUIT		
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm) .x ± .03 (.8) .xxx ± .005 (.127) .xx ± .01 (.25) ANGLES ± 5°			MATERIAL: SEE NOTES SHEET 1		
							THIRD ANGLE PROJECTION			DRAWING NUMBER: 10F113AB-DC		

2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

24 FIBER DUPLEX LC CASSETTE - MODIFIED METHOD A, PAIR FLIPPED	
PART NUMBER	DESCRIPTION
FC2Z0-24-10AF	24 FIBER 50/125um OM4 OPTIMIZED
FC2ZN-24-10AF	24 FIBER 50/125um OM4
FC2X0-24-10AF	24 FIBER 50/125um OM3 OPTIMIZED
FC2XN-24-10AF	24 FIBER 50/125um OM3
FC25N-24-10AF	24 FIBER 50/125um OM2
FC26N-24-10AF	24 FIBER 62.5/125um OM1
FC29N-24-10AF	24 FIBER 9/125um OS1/OS2
FC2SA-24-10AF	24 FIBER 50/125um OM4+, SIGNATURE CORE
FC2WA-24-10AF	24 FIBER 50/125um OM5+, SIGNATURE CORE
FC29N-24-LAAF	24 FIBER OS2 LC/APC, STANDARD LOSS



MODIFIED METHOD A, PAIR FLIPPED - FIBER LAYOUT

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	TITLE				DRAWING NUMBER:	
							24 FIBER DUPLEX LC CASSETTE MODIFIED METHOD A, PAIR FLIPPED				10F113AB-DC	
							CUSTOMER DRAWING				SEE NOTES SHEET 1	
							ITEM REVISION NAME 10F113AB/07				DRAWING NUMBER: 10F113AB-DC	
							DATASET FILE NAME 10F113AB_DC/07B				MATERIAL: SEE NOTES SHEET 1	
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)				DRAWING NUMBER: 10F113AB-DC	
							.x ± .03 (.8) .xxx ± .005 (.127) .xx ± .01 (.25) ANGLES ± 5 °				DRAWING NUMBER: 10F113AB-DC	
							THIRD ANGLE PROJECTION				DRAWING NUMBER: 10F113AB-DC	
							DRAWN BY SAT				DATE 10-01-12	
							CHK TMSE				SCALE NONE	
							DESCRIPTION				SHT 3 OF 3	
							ECN				SIZE A	

2

1