

EL2P Intelligent PDU

Elevate to Power: Smarter. Simpler. More Secure
Way to Manage and Distribute Rack Power

The Future of Rack Power Management

Built with the modern rack in mind, the EL2P PDU saves you time and money by delivering faster installs, smarter visibility, and zero complexities, designed for the real-world challenges of powering today's digital infrastructure.

Top Features & Benefits



Smart Auto Rotating Touchscreen

Simplifies deployment with an adaptive display that flips to match any orientation top or bottom fed.



Secure Zero-Touch Provisioning

Optimizes operational efficiency and reduces errors during initial deployment.



360° Cord Rotation

Innovative cord entry pivots to reduce strain and fit tight enclosures with ease.



Built-In Data Collection

Eliminates the need for external hardware, everything is integrated for simplicity and speed.



Advanced Connectivity

Engineered for secure, real-time access with dual 1Gb ports and lockable high-density outlets.




Aqua Visibility

New aqua-colored outlet banks stand out in dense server environments, enhancing traceability and reducing errors.



Security That Goes Beyond the Standard

- USGv6 Certified IPV6 Stack
- 802.1x MIL-Grade Authentication
- Code Signing & Secure Boot
- Repeat login block access + session timeouts
- Enforced password updates



Seamless Integration

- Role-based access control for centralized security
- Compatible with major platforms through Redfish API and SNMP
- Third-party DCIM ready



Discover Why the EL2P PDU Series is Power, Reimagined

For more information, visit panduit.com/el2p

Specifications

Part Number	Region	Input Current (A) per Phase	Form Factor	Input Plug Type	# of CB's	Apparent Power (kVA)	Outlet Count	Outlet Type	Input Phase	Height in. (mm)	Width in. (mm)	Depth in. (mm)	PDU Type
-------------	--------	-----------------------------	-------------	-----------------	-----------	----------------------	--------------	-------------	-------------	-----------------	----------------	----------------	----------

METERED INPUT PDU

E42D04L	EMEA	32	OU FULL	IEC 60309 3P+N+E 6h 32A (IP44)	6	22	42	(21)C13/C15, (21)C13/C15/ C19/C21	3	70 (1780)	2 (58)	3 (75)	MI
E42D06L					3	7.4		(18)C13/C15, (18)C13/C15/ C19/C21	1				
E36D06L					2		36						
E48D31L	NA/ EMEA	63/60	OU WIDE	IEC 60309 3P+N+E 6h 63A/60A (IP44)	12	34.6/43.5	48	(24)C13/C15, (24)C13/C15/ C19/C21	3	65 (1640)	3 (85)		MS
E36D25L	NA	30	OU FULL	NEMA L6-30P	2	5	36	(18)C13/C15, (18)C13/C15/ C19/C21	1	70 (1780)	2 (58)		
E36E09L	EMEA	32		IEC 60309 3P+N+E 6h 32A (IP44)	6	22		3					

MONITORED SWITCH PDU

E36F13L	EMEA	32	OU FULL	IEC 60309 3P+N+E 6h 32A (IP44)	6	22	36	(18)C13/C15, (18)C13/C15/C19/C21	3	70 (1780)	2 (58)	3 (75)	MPO
----------------	------	----	---------	--------------------------------	---	----	----	----------------------------------	---	-----------	--------	--------	-----

MONITORED SWITCH PER OUTLET PDU

E42G20L	NA	60	OU FULL	IEC 60309 3P+E 9h 60A (IP44)	6	17.3	42	(21)C13/C15, (21)C13/C15/ C19/C21	3	70 (1780)	2 (58)	3 (75)	MSPO
E42G05L	NA/ EMEA	32/30		IEC 60309 3P+N+E 6h 32A/30A (IP44)		17.3/22.0							
E36G18L	NA	30		NEMA L6-30P	2	5	36	(18)C13/C15, (18)C13/C15/ C19/C21	1				
E48G01L	NA/ EMEA	63/60	OU WIDE	IEC 60309 3P+N+E 6h 63A/60A (IP44)	12	34.6/43.5	48	(24)C13/C15, (24)C13/C15/ C19/C21	3	65 (1640)	3 (85)		
E42G03L		32/30	OU FULL	IEC 60309 2P+E 6h 32A/30A (IP44)	3	7.4/5.0	42	(21)C13/C15, (21)C13/C15/ C19/C21	1	70 (1780)	2 (58)		
E48G04L	NA	30		NEMA L15-30P		8.6			3				
E42G02L		60		IEC 60309 2P+E 6h 60A (IP44)	6	10			1				
E36G19L		30		NEMA L21-30P	3	8.6	36	(18)C13/C15, (18)C13/C15/ C19/C21	3				

More models available at panduit.com