



Laser/Ink Jet Labels

PANDUIT[®]

infrastructure for a connected world

Panduit is a global leader in reliable and innovative solutions for identification and safety. Products are engineered for a wide variety of industrial applications – including electrical, electronics, industrial, and network. Panduit offers a complete leading-edge line of labeling software and high-performance label materials (all RoHS compliant) that provide enhanced productivity, dependability, and value to all infrastructure labeling requirements. Laser/Inkjet Labels are on 8.5" x 11" sheets.



Cable/Wire Labels

Turn-Tell® Labels.....	4
Self-Laminating Polyester Labels.....	5
Self-Laminating Tedlar® Labels	6
LabelCore™ Fiber Optic Cable Identification System...	6
Non-Laminated Polyolefin Labels	7

Component Labels


Polyester Component Labels	8
Tedlar® Component Labels.....	9
Non-Adhesive Polyester Network Labels.....	9
Polyolefin Network Labels	10

Labeling Software

Easy-Mark Plus™ Software.....	10
-------------------------------	----

Tedlar is a registered trademark of E. I. du Pont de Nemours and Company.

Turn-Tell® Labels



- Labels rotate and slide along cables after installation for visibility from any angle, and allow repositioning on the wire/cable to align legends for improved aesthetics
- Ideal for use in high-density or space-constrained cable applications
- Use in a wrap format application. Not recommended for flag format applications
- Eliminate the need to disconnect wire or replace label in the event of re-termination
- Temperature range: -65°F to 225°F (-54°C to 107°C)

FEATURED

Part Number	Print-On Area Color	Width		Length		Print-On Area Height		Min. Cable O.D.		Max. Cable O.D.		Wire/Cable Size Range	Labels Per Row	Labels Per Sheet	Labels Per Pkg
		in	mm	in	mm	in	mm	in	mm	in	mm				
R050X75X1J				0.75	19.1	0.25	6.4	0.12	3.1	0.16	4.1	Category 6 28 AWG / 18 – 14 AWG		84	5000
R050X125X1J				1.25	31.8	0.38	9.7	0.16	4.1	0.22	5.6	Category 3 UTP / 12 – 10 AWG		60	
R050X150X1J				1.50	38.1	0.50	12.7	0.22	5.6	0.28	7.1	Category 5e UTP / Category 6 UTP / Category 6A UTP / Cat. 5e FTP / 10 – 6 AWG		48	
R100X075X1J				0.75	19.1	0.25	6.4	0.12	3.1	0.16	4.1	Category 6 28 AWG / 18 – 14 AWG		42	2500
R100X125X1J				1.25	31.8	0.38	9.7	0.16	4.1	0.22	5.6	Category 3 UTP / 12 – 10 AWG		30	
R100X150X1J												Category 5e UTP / Cat. 6 UTP / Category 6A UTP / Cat. 5e FTP / 10 – 6 AWG	6	24	
R100X150X2J	TIA Blue	1.00	25.4	1.50	38.1	0.50	12.7	0.22	5.6	0.28	7.1	Category 5e UTP / Cat. 6 UTP / Category 6A UTP / Cat. 5e FTP / 10 – 6 AWG			
R100X150X7J	TIA Red														
R100X150X8J	TIA Yellow														
R100X225X1J	White			2.25	57.2	0.75	19.1	0.28	7.1	0.39	9.9	Category 6 FTP / Cat. 6A UTP / Category 6A FTP / 8 – 4 AWG		18	1000
R100X400X1J				4.00	101.6	1.00	25.4	0.39	9.9	0.95	24.1	2 – 1 AWG		12	
R150X150X1J		1.50	38.1									Category 5e UTP/ Cat. 6 UTP/ Category 6A UTP/ Cat. 5e FTP / 10 – 6 AWG	4	16	
R200X150X1J				1.50	38.1	0.50	12.7	0.22	5.6	0.28	7.1	Category 5e UTP/ Cat. 6 UTP/ Category 6A UTP/ Cat. 5e FTP / 10 – 6 AWG		12	
R200X225X1J	White			2.25	57.2	0.75	19.1	0.28	7.1	0.39	9.9	Category 6 FTP / Cat. 6A UTP / Category 6A FTP / 8 – 4 AWG	3	9	
R200X400X1J		2.00	50.8									2 – 1 AWG		6	500

Order number of labels required in multiples of Standard Package Quantity.

Self-Laminating Polyester Labels



- Include a colored print-on area and clear over-laminate to protect the legend for clear and durable identification
- Labels are sized specifically for wire and cable applications
- Provide durability; high-temperature resistance, and dimensional stability; do not stretch or easily tear; preferred material for wire/cable labeling
- Use in a wrap format application. Not recommended for flag format applications
- White labels are ASTM E-595 rated for airspace handling
- Temperature Range: -65°F to 225°F (-54°C to 107°C)
- For YAJ parts only: UL recognized, UL969, File # MH14979

	Part Number	Print-On Area Color	Width		Length		Print-On Area Height		Min. Cable O.D.		Max. Cable O.D.		Wire/Cable Size Range	Labels Per Row	Labels Per Sheet	Labels Per Pkg
			in	mm	in	mm	in	mm	in	mm	in	mm				
FEATURED	S050X075YAJ	White	0.50	12.7	0.75	19.1	0.25	6.4	0.08	2.0	0.16	4.0	Category 6 28 AWG/18 – 14 AWG	13	169	5000
FEATURED	S050X125YAJ				1.25	31.8	0.38	9.7	0.12	3.1	0.28	7.0	Category 3 UTP/12 – 10 AWG		104	
FEATURED	S050X150YAJ				1.50	38.1	0.50	12.7	0.16	4.0	0.32	8.1	Category 5e UTP/ Category 6 UTP/ Category 6A UTP/Category 5e FTP/10 – 6 AWG		78	
	S075X075YAJ		0.75	19.1	0.75	19.1	0.25	6.4	0.08	2.0	0.16	4.0	Category 6 28 AWG/18 – 14 AWG	9	117	2500
FEATURED	S075X125YAJ				1.25	31.8	0.38	9.7	0.12	3.1	0.28	7.0	Category 3 UTP/12 – 10 AWG		72	
FEATURED	S075X150YAJ				1.50	38.1	0.50	12.7	0.16	4.0	0.32	8.1	Category 5e UTP/ Category 6 UTP/ Category 6A UTP/Category 5e FTP/10 – 6 AWG		54	
FEATURED	S100X075YAJ		1.00	25.4	0.75	19.1	0.25	6.4	0.08	2.0	0.16	4.0	Category 6 28 AWG/18 – 14 AWG	7	91	2500
FEATURED	S100X125YAJ				1.25	31.8	0.38	9.7	0.12	3.1	0.28	7.0	Category 3 UTP/12 – 10 AWG		56	
BEST SELLER	S100X150YAJ				1.50	38.1	0.50	12.7	0.16	4.0	0.32	8.1	Category 5e UTP/Category 6 UTP/Category 6A UTP/Category 5e FTP/10 – 6 AWG		42	
FEATURED	S100X150YBJ		TIA Blue													
	S100X150YDJ		TIA Green													
	S100X150YFJ		TIA Orange													
	S100X150YHJ	TIA Red														
BEST SELLER	S100X150YIJ	TIA Yellow														
BEST SELLER	S100X225YAJ	White	1.00	25.4	2.25	57.2	0.75	19.1	0.24	6.1	0.48	12.1	Category 6 FTP/ Category 6A UPT/ Category 6A FTP/8 – 4 AWG	8	32	1000
	S100X225YBJ	TIA Blue														
	S100X225YDJ	TIA Green														
	S100X225YFJ	TIA Orange														
	S100X225YHJ	TIA Red														
	S100X225YIJ	TIA Yellow														
FEATURED	S100X400YAJ	White	1.00	25.4	4.00	101.6	1.00	25.4	0.32	8.1	0.95	24.3	2 – 1 AWG	7	14	1000
FEATURED	S100X650YAJ	White			6.50	165.1	1.50	38.1	0.48	12.1	1.59	40.4	1/0 – 350 MCM		7	
	S150X400YAJ	White	1.50	38.1	4.00	101.6	1.00	25.4	0.32	8.1	0.95	24.3	2 – 1 AWG	5	14	1000
FEATURED	S200X150YAJ	White	2.00	50.8	1.50	38.1	0.50	12.7	0.16	4.0	0.32	8.1	Category 5e UTP/ Category 6 UTP/ Category 6A UTP/Category 5e FTP/10 – 6 AWG	4	24	
FEATURED	S200X225YAJ	White			2.25	57.2	0.75	19.1	0.24	6.1	0.48	12.1	Category 6 FTP/Category 6A UPT/Category 6A FTP/8 – 4 AWG		16	
FEATURED	S200X400YAJ	White			4.00	101.6	1.00	25.4	0.32	8.1	0.95	24.3	2 – 1 AWG		8	
FEATURED	S200X650YAJ	White			6.50	165.1	1.50	38.1	0.48	12.1	1.59	40.4	1/0 – 350 MCM		4	

Order number of labels required in multiples of Standard Package Quantity.

For service and technical support, call 1-800-777-3300.

Self-Laminating Tedlar® Labels



- Include a colored print-on area and clear over-laminate to protect the legend for clear and durable identification
- Labels are sized specifically for wire and cable applications
- Labels are self-extinguishing
- Use in a wrap format application. Not recommended for flag format applications
- Temperature range: 0°F to 275°F (-18°C to 135°C)
- UL Recognized: UL969, File # MH 14576, CUL Recognized: C22.2 No 0.15-01, File # MH 14576

Part Number	Print-On Area Color	Width		Length		Print-On Area Height		Min. Cable O.D.		Max. Cable O.D.		Wire/Cable Size Range	Labels Per Row	Labels Per Sheet	Labels Per Pkg
		in	mm	in	mm	in	mm	in	mm	in	mm				
S100X150TAJ-A	White	1.00	25.4	1.50	38.1	0.50	12.7	0.16	4.0	0.32	8.1	Category 5e UTP/ Category 6 UTP/ Category 6A UTP/ Category 5e FTP/ 10 – 6 AWG	7	42	2500

Tedlar® is a registered trademark of E. I du Pont de Nemours and Company.

LabelCore™ Fiber Optic Cable Identification System

PATENTED




- Provides a larger labeling surface on small fiber cables and allows legends to be clearly seen
- Sleeve is made of flexible PVC material
- Locate sleeve on straight section of cable at least 2 inches from fiber boot

Part Number	Color	Part Description	Std Pkg Qty
NWSLC-2Y	Yellow	Yellow cable identification sleeve for 2mm simplex fiber cable, 1 inch long, 100 per pack, use with labels: S100X150YAJ (Laser/Inkjet); S100X150VAM (MP300 Hand-held Printer); S100X150VATY (Thermal Transfer Printer).	100
NWSLC-2Y-AQ	Aqua	Aqua cable identification sleeve for 2mm simplex cable, 1 inch long, 100 per pack, use with labels: S100X150YAJ (Laser/Inkjet); S100X150VAM (MP300 Hand-held Printer); S100X150VA1Y or S100X150VATY (Thermal Transfer Printer).	
FEATURED NWSLC-3Y	Orange	Orange cable identification sleeve for 3mm simplex cable, 1 inch long, 100 per pack, use with labels: S100X150YAJ (Laser/Inkjet); S100X150VAM (MP300 Hand-held Printer); S100X150VA1Y or S100X150VATY (Thermal Transfer Printer).	
FEATURED NWSLC-7Y	White	White cable identification sleeve for 3mm duplex fiber cable, 1 inch long, 100 per pack, use with labels: S100X225YAJ (Laser/Inkjet); S100X225VAM (MP300 Hand-held Printer); S100X225VATY or S200X225VATY (Thermal Transfer Printer).	
NWSLC2-2Y	Yellow	Yellow cable identification sleeve for 2mm simplex cable, 2 inches long, 100 per pack, use with labels: S200X150YAJ (Laser/Inkjet) or S200X150VATY (Thermal Transfer Printer).	
NWSLC2-2Y-AQ	Aqua	Aqua cable identification sleeve for 2mm simplex cable, 2 inches long, 100 per pack, use with labels: S200X150YAJ (Laser/Inkjet) or S200X150VATY (Thermal Transfer Printer).	
NWSLC2-3Y	Orange	Orange cable identification sleeve for 3mm simplex cable, 2 inches long, 100 per pack, use with labels: S200X150YAJ (Laser/Inkjet) or S200X150VATY (Thermal Transfer Printer).	
NWSLC2-7Y	White	White cable identification sleeve for 3mm duplex fiber cable, 2 inches long, 100 per pack, use with labels: S200X225YAJ (Laser/Inkjet) S200X225VATY (Thermal Transfer Printer).	

Order number of sleeves by Standard Package Quantity.

Non-Laminated Polyolefin Labels



- Use as wrap-around label or flag-style marker for wire/cable labeling
- Temperature range: -40°F to 180°F (-40°C to 82°C)
- Conformable material for general identification

Part Number	Color	Width		Length		Min. Cable O.D.		Max. Cable O.D.		Wire/Cable Size Range	Labels Per Row	Labels Per Sheet	Labels Per Pkg
		in	mm	in	mm	in	mm	in	mm				
N025X150FJJ	White			1.50	38.1	0.24	6.1	0.40	10.2	8 – 2 AWG	67	150	10000
N050X075FJJ				0.75	19.1	0.12	3.1	0.16	4.1	12 – 10 AWG	14	154	
N050X125FJJ		0.50	12.7	1.25	31.8	0.20	5.1	0.32	8.1	10 – 6 AWG		98	
N050X150FJJ				1.50	38.1	0.24	6.1	0.40	10.2	8 – 2 AWG		84	
N100X150FJJ				1.50	38.1	0.24	6.1	0.40	10.2	8 – 2 AWG	7	42	

Order number of labels required in multiples of Standard Package Quantity.

Polyester Component Labels



- Used to identify patch panels, faceplates, punch-down blocks, and other network systems hardware
- Used to identify electrical and electronic components and devices

- Temperature range: -40°F to 311°F (-40°C to 154°C)
- UL recognized, UL969, File# MH14979
- cUL recognized, C22.2 No. 0.15-01, File# MH14979

Part Number	Color	Width		Height		Labels Per Row	Labels Per Sheet	Labels Per Pkg
		in	mm	in	mm			
C038X038YJJ	White	0.38	9.7	0.38	9.7	16	352	10000
C050X044YJJ		0.50	12.7	0.44	11.2	13	247	
C060X020YJJ		0.60	15.2	0.20	5.1	11	385	
C075X025YJJ		0.75	19.1	0.25	6.4	9	270	
C075X050YJJ				0.50	12.7		153	
C080X020YJJ		0.80	20.3	0.20	5.1	8	280	
C100X025YJJ		1.00	25.4	0.25	6.4	7	210	
C100X038YJJ				0.38	9.7		140	
C100X050YJJ				0.50	12.7		119	
C150X050YJJ		1.50	38.1	0.50	12.7	5	80	
C150X075YJJ				0.75	19.1		60	
C160X020YJJ		1.60	40.6	0.20	5.1	4	140	5000
C200X050YJJ		2.00	50.8	0.50	12.7		64	
C200X100YJJ				1.00	25.4	28		
C275X125YJJ		2.75	69.9	1.25	31.8	6	18	1000
C300X038YJJ		3.00	76.2	0.38	9.7	2	40	
C300X100YJJ				1.00	25.4		18	
C400X100YJJ		4.00	101.6	1.00	25.4	2	20	
C400X200YJJ				2.00	50.8		10	
C788X050YJJ		7.88	200.2	0.50	12.7	1	16	
C850X1100YJJ	8.50	215.9	11.00	279.4	1		1	25

Order number of labels required in multiples of Standard Package Quantity.

Tedlar® Component Labels



- Self-extinguishing and ideal for labeling high-temperature areas
- Temperature range: -40°F to 275°F (-40°C to 135°C)
- UL969 recognized, File # MH 14576, CUL recognized, C22.2 No 0.15-01, File # MH 14676

Part Number	Color	Width		Height		Labels Per Row	Labels Per Sheet	Labels Per Pkg
		in	mm	in	mm			
C050X125TJJ	White	0.5	12.7	1.25	31.8	5	80	1000
C090X025TJJ		0.9	22.9	0.25	6.4	8	224	5000
C100X038TJJ		1	25.4	0.38	9.7	7	140	
C200X038TJJ		2	50.8	0.38	9.7	3	60	1000

Order number of labels required in multiples of Standard Package Quantity.
 Tedlar® is a registered trademark of E. I du Pont de Nemours and Company.

Non-Adhesive Polyester Network Labels



- Used to identify patch panels, faceplates, and other systems hardware
- Temperature range: -10°F to 150°F (-23°C to 65°C)
- Die-cut labels designed to provide maximum aesthetic quality and appearance

Part Number	Color	Width		Height		Application	Labels Per Row	Labels Per Sheet	Labels Per Pkg
		in	mm	in	mm				
C195X040Y1J	White	1.95	49.5	0.4	10.2	Single-gang faceplate	3	60	1000
C261X035Y1J		2.61	66.3	0.35	8.9	4-port identifier	2	48	
C390X030Y1J		3.9	99.1	0.3	7.6	6-port identifier		48	

Order number of labels required in multiples of Standard Package Quantity.

Polyolefin Network Labels



- Used to identify patch panels, faceplates, and other systems hardware
- Used to identify electrical and electronic components and devices
- Temperature range: -40°F to 180°F (-40°C to 82°C)

Part Number	Color	Width		Height		Type of Application	Labels Per Row	Labels Per Sheet	Labels Per Pkg
		in	mm	in	mm				
C061X030FJJ	White	0.61	15.5	0.30	7.6	1-port identifier	13	325	5000
C125X030FJJ		1.25	31.8	0.30	7.6	2-port identifier	6	150	2500
C188X030FJJ		1.88	47.8	0.30	7.6	3-port identifier	4	100	1000
C200X100FJJ		2.00	50.8	1.00	25.4	General identifier		36	
C252X030FJJ		2.52	64.0	0.30	7.6	4-port identifier	3	75	
C261X030FJJ		2.61	66.3	0.30					
C379X030FJJ		3.79	96.3	0.30	7.6	6-port identifier	2	50	

Order number of labels required in multiples of Standard Package Quantity.

Easy-Mark Plus™ Labeling Software

PATENTED

- Quickly create complex labels or design detailed labels with multiple zones and objects
- Advanced features such as “drag and drop” functionality and wizard tools
- Labels appear on-screen as they will when printed, eliminating guesswork
- Multiple versions available for greater flexibility
- Use with all existing Panduit Easy-Mark™ and Pan-Mark™ files designed in the past, or update them with new objects and styling

System Requirements:


- 300 MB hard drive space and 2 GB Memory
- 32 or 64-bit operating systems
- Windows 7, 8, 8.1, 10 or 11
- Microsoft.NET Framework 4.0 or higher
- Mouse or compatible pointing device
- Keyboard
- Optical Disc Drive or USB Port



FEATURED

Part Number	Description	Std Pkg Qty	Std Pkg Qty
EMPLUS-CD	Easy-Mark Plus™ Labeling Software, CD-ROM	1	10
EMPLUS-DL	Easy-Mark Plus™ Labeling Software, online download		
EMPLUS-2GO	Easy-Mark Plus™ Labeling Software, USB Flash Drive		
EMPLUS-SERVER	Easy-Mark Plus™ Labeling Software, networkable server based version		

^Windows is a registered trademark of Microsoft Corp. in the United States and/or other countries.



PANDUIT®

Panduit Corp.
World Headquarters
Tinley Park, IL 60487

cs@panduit.com
US and Canada: 800.777.3300
Europe, Middle East, and Africa:
44.20.8601.7200
Latin America: 52.33.3777.6000
Asia Pacific: 65.6305.7575

www.panduit.com