


SENSOR IDENTIFICATION LABEL



PANDUIT P/N	WEIGHT
EB001	0.125kg

SPECIFICATION:


- 1. STANDARD
 - TEMP MEASURING RANGE: 0°C - 65°C [32°F - 149°F]
 - TEMP MEASUREMENT ACCURACY: ± 2%
 - TEMP OPERATING RANGE: 0°C - 65°C [32°F - 149°F]
 - HUMIDITY MEASURING RANGE: 10-90% RH
 - HUMIDITY MEASUREMENT ACCURACY: ±8% RH @ 5°C-50°C [41°F-122°F]
 - HUMIDITY OPERATING RANGE: 10-90% RH, NON-CONDENSING
 - OPERATIONAL VOLTAGE: 5 ±0.1 VOLTS DC
 - CURRENT DRAW: 30 mA MAX
 - SENSOR HOUSING MATERIAL: ABS, 10% GLASS-FILLED
 - SENSOR HOUSING COLOR: BLACK
 - INTERFACE PLUG: RJ45 COMPLIANT
 - INTERFACE PLUG HOUSING MATERIAL: PC
 - INTERFACE PLUG HOUSING COLOR: TRANSPARENT
 - LABEL CONTENT: T/RH
- 2. ADDITIONAL: NONE
- 3. ACCESSORY COMPONENTS:
 - CABLE TIES, QTY:(5)
 - INSTALLATION GUIDE, QTY:(1)

NOTES:

- 1. PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSION ARE IN INCHES
- 2. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
- 3. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART

IDENTIFICATION

PART NUMBER	DESCRIPTION
EB001	TEMPERATURE AND HUMIDITY SENSOR KIT



WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.

SIGN _____
DATE _____
PRINT _____

TITLE: SMARTZONE G5
TEMPERATURE AND HUMIDITY SENSOR KIT
CUSTOMER DRAWING

ITEM REVISION NAME: _____
DATASHEET FILE NAME: _____

UNLESS OTHERWISE SPECIFIED
DIMENSIONAL TOLERANCE ARE: mm [IN]
Wire Harness
Tolerance(mm)

MATERIAL/COLOR: N/A

THIRD ANGLE PROJECTION

DRAWING NUMBER: EB001_DC

DRAWN BY: Hanson DATE: 11/01/2017 CHK: MM SCALE: NONE

SHT 1 OF 1

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00A	11/01/2017	Hanson	MM	DJB	INITIAL RELEASE	EB001

B

A

B

A

2

1

2

1