

## The Safe and Secure Campus



When it comes to safety and security in school settings, most campuses today react to the reality that is ripped from the headlines. Security cameras keep an ever-present eye on not only buildings, but also parking lots and walkways.

Controlled access at doors limits those who can get inside buildings. Security staff monitor video surveillance to help prevent emergencies. Safety systems automatically alert local emergency services if an alarm sounds. It's all part of a global effort to keep students, faculty, and staff safe.

When safety and security are critical, you need a network infrastructure that ties it all together, and makes it easy to use and monitor. Panduit structured cabling solutions deliver reliable performance for these critical systems, including a full plenum offering for mounting and connecting security cameras in the ceiling; small diameter patch cords and high-density patching solutions help provide the space you need to connect backup systems and associated equipment in the telecommunications room.

∴ 93% of public schools control access to campus buildings; 75% use security cameras to monitor buildings and grounds  
– National Center for Education Statistics

Part Number	Part Description
-------------	------------------

### Horizontal Cables



<b>PUP6AHD04BU-G</b>	Category 6A U/UTP copper cable with Vari-MaTriX™ HD Technology, plenum, 4-pair, Blue.
<b>PUFP6X04BU-UG</b>	Category 6A U/FTP copper cable, plenum, 4-pair, Blue.
<b>PUP6004BU-W</b>	Category 6 U/UTP copper cable, plenum, 4-pair, Blue.
<b>PUO6C04BL-U</b>	Category 6 outside plant U/UTP copper cable with gel-filled construction to prevent moisture migration in underground or wet applications, 4-pair, Black.

### Patch Cords



<b>UTP28X3BU</b>	Category 6A performance, 28 AWG, UTP patch cord, CM/LSZH, Blue, 3 ft.
<b>STP28X10MBU</b>	Category 6A performance, 28 AWG, F/UTP patch cord, CM/LSZH, Blue, 10m.
<b>UTP28SP3BU</b>	Category 6 performance, 28 AWG, UTP patch cord, CM/LSZH, Blue, 3 ft.

### RJ45 Modules



<b>FP6X88MTG</b>	Category 6A UTP field term RJ45 plug for field termination of 4-pair unshielded twisted pair cable.
<b>FPS6X88MTG</b>	Category 6A shielded field term RJ45 plug for field termination of 4-pair shielded twisted pair cable.
<b>FC-ICCP1MBU</b>	TX6A™ Category 6A UTP FieldCord™ Connector for field termination of 4-pair UTP cable to connect devices with confined port spaces.
<b>FC-OCC/O5MBL</b>	TX6A™ Category 6A Shielded/Outdoor FieldCord™ Connector for field termination of 4-pair shielded cable to connect devices with confined port spaces in outdoor or shielded environments.
<b>CJ6X88TGBU</b>	Category 6A, RJ45, 8-position, 8-wire UTP jack module with MaTriX Technology.
<b>CJS6X88TGY</b>	Category 6A, RJ45, 8-position, 8-wire shielded jack module with MaTriX Technology.
<b>NK6X88MBU</b>	Category 6A, 8-position, 8-wire keystone punchdown jack module.
<b>CJ688TGBU</b>	Category 6, RJ45, 8-position, 8-wire jack module. UL Rated: UL 1863 and UL 2043.
<b>CJS688TGY</b>	Category 6, RJ45, 8-position, 8-wire shielded jack module. UL Rated: UL 1863 and UL 2043.
<b>NK688MBU</b>	Category 6, 8-position, 8-wire keystone punchdown jack module.

### Physical Security Products



<b>SKRJ45RD-X</b>	SmartKeeper RJ45 jack module blockout device; requires master key (SKMKEY) to unlock and remove.
<b>SKUSBA-V</b>	SmartKeeper USB Type A blockout device; requires master key (SKMKEY) to unlock and remove.
<b>SKUSBC</b>	SmartKeeper USB Type C blockout device; requires master key (SKMKEY) to unlock and remove.
<b>SKMKEY</b>	SmartKeeper master key for removal of all SmartKeeper blockout devices.

### Accessories



<b>CBX2IW-AY</b>	Mini-Com® 2-port Surface Mount Box accepts up to two Mini-Com® Modules. UL Rated: UL 1863 and UL 2043; Off White.
<b>NK2BXIW-A</b>	NetKey® 2-port Surface Mount Box accepts up to two NetKey® Modules; Off White. Note: Not UL rated for use in plenum spaces.

See [www.panduit.com](http://www.panduit.com) for additional colors, sizes, cable jackets, and performance offerings.

#### WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA  
Phone: 800.777.3300

PANDUIT EUROPE LTD.  
London, UK  
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.  
Republic of Singapore  
Phone: 65.6305.7575

PANDUIT JAPAN  
Tokyo, Japan  
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA  
Guadalajara, Mexico  
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.  
Victoria, Australia  
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to [www.panduit.com/warranty](http://www.panduit.com/warranty)

**PANDUIT**®

For more information  
Visit us at [www.panduit.com](http://www.panduit.com)  
Contact Customer Service by email: [cs@panduit.com](mailto:cs@panduit.com)  
or by phone: 800.777.3300

© 2022 Panduit Corp.  
ALL RIGHTS RESERVED.  
CPAG06--SA-ENG  
6/2022