



Robust Physical Infrastructure for Technologically-Advanced Surgical Care

The COVID-19 pandemic changed much about hospitalizations, with hospitals recommitting to delivering safe, efficient spaces and procedures to protect patients, their families, and staff. Nowhere is that safety more critical than in operating rooms. When designed to accommodate the latest technologies, they help organizations improve their facility's capacity, patient outcomes, efficiencies, and productivity. State-of-the-art designs enable top-notch surgeons to create the best outcomes, and provide the best overall patient experience.

The right type of infrastructure helps to address many of the challenges and demands on the network:

- On-demand patient record retrieval
- Live teleconferencing with specialists around the world
- Surgical robotics
- Efficient routing, recording, transmission, and storage of data
- Artificial intelligence


A robust, high-performance cabling system supports both wired and wireless connectivity to meet the medical technology demands of today and the future. Investing in a robust physical infrastructure layer provides the foundation for the most technologically-advanced surgical care.

Panduit is committed to providing quality, top-performing structured cabling products that enable:

- Fast, secure data transmission and efficient Power over Ethernet built around the Vari-MaTriX Category 6A copper cabling system
- Clear, responsive AV experiences with our end-to-end AV solution including active devices from Atlona, a Panduit company
- Reliable wireless capabilities connected by structured cabling and easy-to-install Field Term Plugs
- Safe, efficient videoconferencing services that protect the health and safety of patients and medical staff



| Part Number | Part Description |
|-------------------------|--|
| Horizontal Cable | |
| PUP6AHD04BU-G | Category 6A U/UTP Vari-MaTriX HD Copper Cable, plenum, 4-pair, Blue. |
| PFP6X04BU-UG | Category 6A F/UTP copper cable, plenum, 4-pair, Blue. |




| | |
|---------------------------|---|
| Copper Patch Cords | |
| UTP6AX3BU | Category 6A performance, 24 AWG, UTP patch cord, CM, Blue, 3 ft. |
| UTP28X3BU | Category 6A performance, 28 AWG, UTP patch cord, CM/LSZH, Blue, 3 ft. |
| STP6X1MBU | Category 6A performance, 26 AWG, S/FTP patch cord, CM, Blue, 3 ft. |
| STP28X1MBU | Category 6A performance, 28 AWG, F/UTP patch cord, CM/LSZH, Blue, 3 ft. |



| | |
|---------------------|---|
| RJ45 Modules | |
| FP6X88MTG | Category 6A UTP field term RJ45 plug for field termination of 4-pair unshielded twisted pair cable. |
| FPS6X88MTG | Category 6A Shielded field term RJ45 plug for field termination of 4-pair shielded twisted pair cable. |
| FC-ICCP1MBU | Category 6A UTP FieldCord Connector for field termination of 4-pair unshielded twisted pair cable. Designed for small connector spaces where traditional plugs and connectors don't fit. |
| CJ6X88TGBU | Category 6A, RJ45, 8-position, 8-wire jack module with MaTriX Technology. Supports high-bandwidth applications and is ideal for running next generation Power over Ethernet (PoE++). UL Rated: UL 1863 and UL 2043. |
| CJS6X88TGY | Category 6A, RJ45, 8-position, 8-wire shielded jack module. Supports high-bandwidth applications. |
| CJH6X88TGBU | Category 6A, RJ45, 8-position, 8-wire jack module with MaTriX Technology, with spring-shuttered jack. Supports high-bandwidth applications and is ideal for running next generation Power over Ethernet (PoE++). UL Rated: UL 1863 and UL 2043. |



| | |
|----------------------------|--|
| Surface Mount Boxes | |
| CBXQ2IW-A | Mini-Com® 2-Port Surface Mount Box accepts up to two Mini-Com® Modules, Off White. Includes quick release cover. UL Rated: UL 1863 and UL 2043. Supplied with cable ties, adhesive backing, label and label cover. |
| CBX1IW-A | Mini-Com® 1-Port Low Profile Surface Mount Box accepts a single Mini-Com® Module, Off White. UL Rated: UL 1863 and UL 2043. Mounts easily with screws or adhesive tape. Accepts cable sizes through Category 6A. |
| CBX2IW-AY | Mini-Com® 2-Port Surface Mount Box accepts up to two Mini-Com® Modules, Off White. Includes built-in removable blank to add a second module. UL Rated: UL 1863 and UL 2043. Mounts easily with screws, adhesive tape or magnet (sold separately). Accepts cable sizes through Category 6A. |



| | |
|-----------------------------------|---|
| Stainless Steel Faceplates | |
| CFPL4SY | Single gang, stainless steel vertical faceplate with label pockets; accepts four Mini-Com® Modules. |



| | |
|--------------------|---|
| Labeling | |
| MP300 | PXE™ Mobile Label Printer. Max label width: 1.5 inches. |
| R100X150V1M | MP Cassette, Turn-Tell Self-Laminating Label, Vinyl, 1.0" w x 1.5" h, 0.5" print on area. |

See www.panduit.com for additional colors, sizes, cable jackets, and performance offerings.