


TDP43ME PRINTER RIBBON SETTING RECOMMENDATIONS

© Panduit Corp. 2015

SETTING THE TDP43ME PRINTER SPEED OR DARKNESS: (For WIN-XP)



NOTE: Click on the ABOUT tab to retrieve current driver version.

In PRINTERS & FAXES (**WIN-XP**), right click on the TDP43ME printer to be controlled. Click on PRINTING PREFERENCES button.

In the OPTIONS tab, set SPEED and DARKNESS.

Default Speed = 2.

Default Darkness = 17

Website: www.panduit.com
Email: id-support@panduit.com

EU Website:
www.panduit.com/emea

EU Email:
emeatoolservicecenter@panduit.com




Technical Support:
Panduit Corp. • ID Products Division
Cumming, GA
Tel: 800-777-3300 • Fax: 708-532-1811

Panduit Europe • EMEA Service Center
Almelo, Netherlands
Tel: +31-546-580-452 • Fax: +31-546-580-441

Panduit Europe • West World Headquarters
Westgate, London
England Tel: 208-601-7200 • Fax: 208-601-7319



SETTING THE TDP43ME PRINTER SPEED OR DARKNESS: (For Windows 7)



← NOTE: Click on the ABOUT tab to retrieve current driver version.

← In DEVICES and PRINTERS (Windows 7), right click on PRINTING PREFERENCES.

In the OPTIONS tab, set SPEED and DARKNESS.

Default Speed = 2.

Default Darkness = 17

TDP43ME PRINTER RIBBON SETTING RECOMMENDATIONS			
Material	Suggested Thermal Transfer Ribbon	Printer Speed	Printer Darkness
Vinyl Self-Lams	Hybrid	2	17
PVDF Self Lams	Hybrid	2	15
Turn-Tell Labels	Hybrid	2	17
Military Grade Heat Shrink Tubing	Hybrid	2	17
Halogen Free Heat Shrink Tubing	Hybrid	2	17
Fluid Resistant Heat Shrink Tubing	Resin-C	2	19
Vinyl Cloth	Hybrid	2	19
Nylon Cloth	Resin	2	15
Continuous Vinyl Tapes	Resin	2	17
Continuous Reflective Tapes	Resin	2	19
Flag Labels	Resin	2	16
Non-Adhesive Polyester	Resin	2	14
White Polyester	Resin	2	10
Silver Polyester	Resin	2	17
Tamper Evident Polyester	Resin	2	19
Super-Tack Polyester	Resin	2	14
Raised Panel Labels	Resin	2	17
Thermal Transfer Marker Plates	Resin	2	17
Flame Retardant Halogen Free Marker Plates	Resin	2	17
Nuclear Rated Marker Plates	Resin	2	19
Paper	Resin	2	15
Tan Kapton	Hybrid	2	15
White Kapton	Resin-C	2	19
Polyolefin	Resin	2	17